

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 20/16mm

Order data

Order number	260935 20/16
GTIN	4045197653611
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	25 mm
suitable indexable insert	TC.. 16T3..
Centre offset L_3	13 mm
Head length L_1	36.6 mm
ISO code toolholder	A20R STFCCR/L16
Pack of insert screws	269028 8
Insert size	16 mm
Overall length L	200 mm
Clamping height L_2	18 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 8	269028 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500