



Whistle Notch side lock arbor Form ADB, BT 40 short, Clamping range \varnothing D1: 25 mm



Order data

Order number	302720 25
GTIN	4250122613305
Item class	36E

Description

Version:

With clamping screw and stop screw.

Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Overhang dimension A: 90 mm

External \varnothing D: 65 mm

Spare clamping screw No. 30 9900: 25

Technical description

Spare clamping screw No. 30 9900	25
Overhang dimension A	90 mm
Clamping \varnothing D ₁	25 mm
External \varnothing D	65 mm
Adapter	BT 40 short
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	ADB

Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull stud 60° sealed suitable for steep tapers 40	308785 40
Pull stud Hurco 60° with fit sealed suitable for steep tapers 40	308804 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Hurco 60° pull stud with bore and fit sealed suitable for steep tapers 40	308803 40
Pull-stud 60° sealed suitable for steep tapers 40	308780 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull stud Hurco 90° with bore and fit sealed suitable for steep tapers 40	308805 40