

**Cordless random orbital sander with rechargeable battery, Type: M18FROS125****Order data**

Order number	077319 M18FROS125
GTIN	4058546521233
Item class	03L

Description**Version:**

M18 FUEL™ cordless random orbital sander with 2.5 mm orbit and 12,000 rpm, which enables a fast and efficient material removal rate. The sander comes with a suction function as well as improved ergonomics and grip.

Supplied with:

Supplied with 2×5.0 Ah Li-ion battery, dust bag, extraction adapter, extension adapter, 2× abrasive paper.

Note:

Suitable 8-hole abrasive disc item No. 567745 and ABRANET item No. 567802.

Technical description

Speed of oscillation	6000 - 12000 min ⁻¹
Backing pad Ø	125 mm
Orbital stroke	2.4 mm
Battery voltage	18 V

Data sheet

Weight	1.9 kg
Battery capacity	5 Ah
maximum vibration to EN	1.5 m/s ²
Packaging	Carrying case
Type of product	Orbital sander