

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 25/16mm

Order data

Order number	260934 25/16
GTIN	4045197653567
Item class	21T

Technical description

suitable indexable insert	TC.. 16T3..
Head length L ₁	41 mm
Centre offset L ₃	17 mm
Minimum pre-drill Ø D _{min}	32 mm
Insert size	16 mm
Pack of insert screws	269028 8
ISO code toolholder	A25R STFCL/L16
Overall length L	200 mm
Clamping height L ₂	23 mm
Setting angle κ	90 degrees
Shank Ø D _s	25 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500