

**Hook turning tool right-hand similar to DIN 4963, HSS E, Shank Ø: 20mm****Order data**

Order number	297120 20
GTIN	4045197190673
Item class	22E

Description**Version:**

All dimensions **welded**.

Application:

Universally applicable, medium cutting speeds.

HSS/E – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

Technical description

for bores from Ø	40 mm
Blade width	5 mm
maximum grooving depth t_{max}	14 mm
Shank Ø	20 mm
Overall length	250 mm
Tool material	HSS E
Type of product	Turning tool