

**Battery / mains radio, Type: 4933493530****Order data**

Order number	073960 4933493530
GTIN	4058546484019
Item class	03L

Description**Version:**

Sturdy site radio, splash-proof (IP54) for mains and battery operation. M18™ Bluetooth® cordless speaker

- **Provides audio for small and medium-sized areas.**
- **Unlimited hanging and attachment options with the integrated hooks, nail hooks and through-holes.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Includes mains cable, 2 back-up batteries, AUX connection cable, without batteries.

Technical description

Battery voltage	18 V
Weight	3.8 kg
Height	333 mm

Data sheet

Width	145 mm
Length	213 mm
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Interface	Bluetooth® interface
Interface	USB interface
IP Index of Protection	IP 54
Type of product	Radio