



Side lock arbor Form ADB with cooling channel, BT 50 short, Clamping range Ø D1: 12 mm



Order data

Order number	302665 12
GTIN	4250122613145
Item class	36E

Description

Version:

Coolant channel bore can be plugged with an O-ring.
All shanks burnished.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Overhang dimension A: 80 mm

External Ø D: 42 mm

Spare clamping screw No. 30 9900: 12

Technical description

Spare clamping screw No. 30 9900	12
Clamping Ø D ₁	12 mm
Overhang dimension A	80 mm
External Ø D	42 mm
Adapter	BT 50 short
Standard	DIN 6359
Arbor standard	ISO 7388-2

Arbor standard	JIS B6339
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull stud 90° sealed suitable for steep tapers 50	308795 50
Pull stud 45° sealed suitable for steep tapers 50	308760 50
Pull-stud 60° sealed suitable for steep tapers 50	308780 50
Torque insert for Pull studs to SO 7388 suitable for steep tapers 50 SK	308812 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50
Pull stud 45° sealed suitable for steep tapers 50	308765 50
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for steep tapers 50 SK	308820 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Torque insert for Pull studs to DIN 69872 suitable for steep tapers 50 SK	308810 50
Wrench for pull studs ISO 7388 suitable for steep tapers 50 SK	308830 50