



Side lock arbor Form ADB, BT 50 short, Clamping range $\varnothing D_1$: 10mm



Order data

Order number	302660 10
GTIN	4250122615712
Item class	36E

Description

Version:

All shanks burnished.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	63 mm
Spare clamping screw No. 30 9900	10
Clamping $\varnothing D_1$	10 mm
External $\varnothing D$	35 mm
Adapter	BT 50 short
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 15,000 rpm

Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Spare clamping screw for chucks with clamping Ø D1 10 mm	309900 10