

**Garant**
**Boring bar steel, right-hand, Shank Ø / insert size: 32/16mm**

**Order data**

Order number	260934 32/16
GTIN	4045197653574
Item class	21T

**Technical description**

Shim screw	269013 2
Insert size	16 mm
Centre offset $L_3$	22 mm
Pack of insert screws	269028 2
ISO code toolholder	A32S STFCL/L16
Head length $L_1$	34.6 mm
Shim	269005 7
Minimum pre-drill $\varnothing D_{\min}$	40 mm
suitable indexable insert	TC.. 16T3..
Overall length L	250 mm
Clamping height $L_2$	30 mm
Setting angle $\kappa$	90 degrees
Shank $\varnothing D_s$	32 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim screw Type 2	269013 2
Set of insert screws Type 8	269028 8
Shim Type 7	269005 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500