



Side lock arbor Form ADB, BT 50 A = 160, Clamping range Ø D1: 14mm



Order data

| | |
|--------------|---------------|
| Order number | 302670 14 |
| GTIN | 4250122619680 |
| Item class | 36E |

Description

Version:

All shanks burnished.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

| | |
|---------------------------------------|---------------------|
| Clamping Ø D ₁ | 14 mm |
| Overhang dimension A | 160 mm |
| Spare clamping screw No. 30 9900 | 12 |
| External Ø D | 44 mm |
| Adapter | BT 50 A = 160 |
| Standard | DIN 6359 |
| Arbor standard | ISO 7388-2 |
| Arbor standard | JIS B6339 |
| Shape | ADB |
| Balance quality G at rotational speed | G 6.3 at 15,000 rpm |

| | |
|--------------------|-----------------|
| Concentricity | ≤ 3 µm |
| Machining strategy | HPC |
| Type of product | Side lock arbor |

Accessories

| | |
|---|-----------|
| Pull stud 90°sealed suitable for steep tapers 50 | 308790 50 |
| Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50 | 308820 50 |
| Pull stud 60°sealed suitable for steep tapers 50 | 308785 50 |
| Pull stud 45°sealed suitable for steep tapers 50 | 308765 50 |
| Wrench for pull studsISO 7388 suitable for ISO taper size 50 | 308830 50 |
| Pull stud 90°sealed suitable for steep tapers 50 | 308795 50 |
| Pull stud 45°sealed suitable for steep tapers 50 | 308760 50 |
| Spare clamping screw for chucks with clamping Ø D1 12 mm | 309900 12 |