

**Parting off tool right-hand similar to DIN 4961, HSS E, Shank height: 16mm****Order data**

Order number	297000 16
GTIN	4045197190345
Item class	22E

**Description****Version:**

All dimensions **welded**.

**Application:**

Universally applicable, medium cutting speeds.

**HSS/E** – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

**Technical description**

Blade width	3 mm
Shank height h	16 mm
Overall length	125 mm
Shank width b	10 mm
Tool material	HSS E
Type of product	Turning tool