

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 40/16mm

Order data

Order number	260934 40/16
GTIN	4045197656063
Item class	21T

Technical description

ISO code toolholder	A40T STFCCR/L16
Insert size	16 mm
suitable indexable insert	TC.. 16T3..
Shim	269005 7
Shim screw	269013 2
Pack of insert screws	269028 2
Centre offset L_3	27 mm
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Head length L_1	37.5 mm
Overall length L	300 mm
Clamping height L_2	39 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	40 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 8	269028 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim screw Type 2	269013 2
Shim Type 7	269005 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500