

**Parting off tool right-hand similar to DIN 4961, HSS E, Shank height: 20mm****Order data**

Order number	297000 20
GTIN	4045197190352
Item class	22E

Description**Version:**

All dimensions **welded**.

Application:

Universally applicable, medium cutting speeds.

HSS/E – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

Technical description

Shank height h	20 mm
Blade width	4 mm
Overall length	140 mm
Shank width b	12 mm
Tool material	HSS E
Type of product	Turning tool