



## Whistle Notch side lock arbor Form ADB, BT 40 short, Clamping range $\varnothing D_1$ : 12 mm



### Order data

Order number	302720 12
GTIN	4250122613251
Item class	36E

### Description

#### Version:

With clamping screw and stop screw.

#### Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Overhang dimension A: 63 mm

External  $\varnothing D$ : 42 mm

Spare clamping screw No. 30 9900: 12

### Technical description

Overhang dimension A	63 mm
Clamping $\varnothing D_1$	12 mm
Spare clamping screw No. 30 9900	12
External $\varnothing D$	42 mm
Adapter	BT 40 short
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	ADB

Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

## Accessories

Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull-stud 60° sealed suitable for steep tapers 40	308780 40
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Pull stud Hurco 90° with bore and fit sealed suitable for steep tapers 40	308805 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Pull stud Hurco 60° with fit sealed suitable for steep tapers 40	308804 40
Hurco 60° pull stud with bore and fit sealed suitable for steep tapers 40	308803 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40