



Hook turning tool right-hand similar to DIN 4963, HSS E, Shank Ø: 6mm



Order data

Order number	297120 6
GTIN	4045197190628
Item class	22E

Description

Version:

All dimensions **welded**.

Application:

Universally applicable, medium cutting speeds.

HSS/E – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

Technical description

for bores from Ø	13 mm
Blade width	2 mm
maximum grooving depth t_{max}	3 mm
Shank Ø	6 mm
Overall length	125 mm
Tool material	HSS E
Type of product	Turning tool