



Eye bolt, Thread Ø: M20



Order data

Order number	086472 M20
GTIN	2050001741783
Item class	08Y

Description

Version:

High-strength eye bolts / nuts, red paint finish.

Note:

Do not place a load on the eye bolt / nut at 90° to the screw thread axis!

SF 4:1 = Safety Factor 4.

Technical description

Thread length of nut E	20 mm
Overall height F	90 mm
Collar Ø support C	50 mm
Internal Ø ring A	50 mm
Weight	0.86 kg
External Ø ring B	90 mm
Thread Ø	M20

Thread length	30 mm
Dimension D	20 mm
Lifting capacity WLL SF 4:1	6 t
Type of product	Eye bolt