

Garant**Side lock arbor Form ADB, SK 40 short, Clamping range \varnothing D1: 6mm****Order data**

Order number	300100 6
GTIN	4045197282705
Item class	31A

Description**Version:**

With Balluff/RFID chip bore.

GARANT –

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	50 mm
Spare clamping screw No. 30 9900	6
Clamping \varnothing D ₁	6 mm
External \varnothing D	25 mm
Adapter	SK 40 short
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull studForm A suitable for steep tapers 40	308600 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
	308630 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studsealed suitable for steep tapers 40	308635 40
Spare clamping screw for chucks with clamping Ø D1 6 mm	309900 6