

**Garant**
**Screw-on toolholder, neutral, Shank / insert size: 16/11mm**

**Order data**

Order number	261111 16/11
GTIN	4045197655837
Item class	21T

**Technical description**

Shank size	16 mm
suitable indexable insert	VB.. 1103..
Overhang L <sub>1</sub> neutral holders	25 mm
Pack of insert screws	269028 22
Overall length L neutral holders	100 mm
Functional width L <sub>4</sub> neutral holders	8 mm
Insert size	11 mm
ISO code toolholder	SVBN 1616H11
Series	QuickTurn
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle $\kappa$	72.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 22

269028 22

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500