

**HOLEX®**
**Side lock arbor Form AD, SK 40 short, Clamping range  $\varnothing$  D1: 32 mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 300200 32     |
| GTIN         | 4045197143709 |
| Item class   | 32A           |

**Description**
**Version:**

With Balluffchip bore.

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Overhang dimension A: 100 mm

External  $\varnothing$  D: 72 mm

Spare clamping screw 309900: 32

**Technical description**

|                                       |             |
|---------------------------------------|-------------|
| Overhang dimension A                  | 100 mm      |
| Spare clamping screw 309900           | 32          |
| Clamping $\varnothing$ D <sub>1</sub> | 32 mm       |
| External $\varnothing$ D              | 72 mm       |
| Adapter                               | SK 40 short |
| Norm                                  | DIN 6359    |
| Arbor standard                        | DIN 69871   |
| Arbor standard                        | ISO 7388-1  |
| Shape                                 | AD          |

|                                       |                     |
|---------------------------------------|---------------------|
| Balance quality G at rotational speed | G 6.3 at 15,000 rpm |
| Concentricity                         | ≤ 3 µm              |
| Machining strategy                    | HPC                 |

## Accessories

|   |            |
|---|------------|
| Pull stud 90° sealed suitable for steep tapers 40                             | 308795 40  |
| Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 40 SK   | 308830 40  |
| Pull stud sealed, form B suitable for steep tapers 40                         | 308650 40  |
| Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK       | 308812 40  |
| Pull stud 45° sealed suitable for steep tapers 40                             | 308760 40  |
| Pull stud sealed, form B suitable for steep tapers 40                         | 308620 40  |
| Pull stud sealed suitable for steep tapers 40                                 | 308635 40  |
| Special pull stud with no internal thread sealed suitable for steep tapers 40 | 308700 40  |
| Pull stud sealed suitable for steep tapers 40                                 | 308660 40  |
| Special pull stud with no internal thread sealed suitable for steep tapers 40 | 308720 40  |
| Pull stud Form A suitable for steep tapers 40                                 | 308600 40  |
| Pull stud Form B suitable for steep tapers 40                                 | 308640 40  |
| Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40     | 308801 40  |
| Pull stud Mazak sealed, form A suitable for steep tapers 40M                  | 308670 40M |
| Pull stud 90° sealed suitable for steep tapers 40                             | 308790 40  |
| Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 40 SK  | 308820 40  |
| Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK     | 308810 40  |

|   |           |
|---|-----------|
| Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40            | 308605 40 |
| Special pull stud with internal thread suitable for steep tapers 40 | 308740 40 |
| Pull stud Hurco 45° with fit sealed suitable for steep tapers 40    | 308802 40 |
| Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40   | 308630 40 |
| Pull stud Hurco 90° with fit sealed suitable for steep tapers 40    | 308806 40 |
| Pull stud 60° sealed suitable for steep tapers 40                   | 308785 40 |
| Pull stud 45° sealed suitable for steep tapers 40                   | 308765 40 |
| Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40    | 308615 40 |
| Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40   | 308625 40 |
| Pull stud stud sealed, form A suitable for steep tapers 40          | 308610 40 |