

Garant
Screw-on toolholder, right-hand, Shank / insert size: 20/11 mm

Order data

Order number	261106 20/11
GTIN	4045197655486
Item class	21T

Technical description

ISO code toolholder	SVHBR/L 2020K11
suitable indexable insert	VB.. 1103..
Shank size	20 mm
Insert size	11 mm
Functional width L ₄	25 mm
Head length L ₁	17 mm
Pack of insert screws	269028 22
Overall length L	125 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500