

Garant
Side lock arbor Form ADB, SK 40 A = 100, Clamping range \varnothing D1: 6mm

Order data

Order number	300230 6
GTIN	4045197282903
Item class	31A

Description
Version:

With Balluff/RFID chip bore.

GARANT –

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Spare clamping screw No. 30 9900	6
Overhang dimension A	100 mm
Clamping \varnothing D ₁	6 mm
External \varnothing D	25 mm
Adapter	SK 40 A = 100
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull studsealed suitable for steep tapers 40	308660 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull studForm A suitable for steep tapers 40	308600 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
	308630 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

Pull stud 90°sealed suitable for steep tapers 40

308790 40

Pull studsealed suitable for steep tapers 40

308635 40

Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40

308615 40

Pull stud 90°sealed suitable for steep tapers 40

308795 40

Special pull stud with no internal threadsealed suitable for steep tapers 40

308700 40

Spare clamping screw for chucks with clamping Ø D1 6 mm

309900 6