

**Garant**

**eco-grooving toolholder, right-hand, Shank width / groove width w:  
25/3Lmm**



## Order data

Order number	273835 25/3L
GTIN	4045197612175
Item class	21W

## Description

### Version:

Made of high-tensile tool steel ( $> 1300 \text{ N/mm}^2$ ). In conjunction with the convex insert clamping, the system achieves very high resistance to axial and radial cutting forces and thereby significantly increases the surface quality and productivity.  $12.5 \times w$  (**groove depth up to 37.5 mm**)

### Note:

Maximum  $\varnothing$  = limited workpiece  $\varnothing$  due to the tool type.

From 19.5 mm groove depth (up to groove width 3 mm) and from 24.5 mm groove depth (from groove width 4 mm) the second cutter comes into contact with the workpiece. This can lead to scoring.

If necessary, use single-cutter grooving inserts No. 273656 – 273670.

Coolant transfer only possible in conjunction with GARANT Master eco toolholders No. 319006 – 319136.

## Technical description

Functional width $L_4$	26.5 mm
Groove width $w$	3 mm
Head length $L_1$	54 mm
Screw	279815 6 (TX25; 6 Nm)
Grooving depth $t_{\max}$	37.5 mm

Overall length L	125.5 mm
Series	Eco
maximum $\varnothing$	75 mm
Shank width b	25 mm
Application type	right-hand
Through-coolant	yes
axial grooving possible	no
Type of product	Boring bar

---

## Accessories

Clamping screw Type 6	279815 6
-----------------------	----------