

Garant**Screw-on toolholder, left-hand, Shank / insert size: 20/11mm****Order data**

Order number	261109 20/11
GTIN	4045197655806
Item class	21T

Technical description

suitable indexable insert	VB.. 1103..
ISO code toolholder	SVJBR/L 2020K11
Insert size	11 mm
Shank size	20 mm
Functional width L ₄	25 mm
Head length L ₁	23 mm
Pack of insert screws	269028 22
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500