



Boring bar steel, right-hand, Shank Ø / insert size: 16/11 mm



Order data

Order number	261120 16/11
GTIN	4960664585557
Item class	25U

Description

Version:

Streamlined flutes for improved chip evacuation, reduced tendency to vibrate, stable machining conditions.

Through-coolant: yes

Shank Ø D_s : 16 mm

ISO code toolholder: A16Q SVUBR/L11

Cutting point / joint: 16 mm

Setting angle κ : 93 degrees

suitable indexable insert: VB.. 1103..

Minimum pre-drill Ø D_{min} : 20 mm

Technical description

Cutting point / joint	16 mm
Centre offset L_3	16 mm
Insert size	11 mm
suitable indexable insert	VB.. 1103..
ISO code toolholder	A16Q SVUBR/L11
Insert screw	269022 6
Minimum pre-drill Ø D_{min}	20 mm
Overhang L_1	65 mm
Overall length L	180 mm
Clamping height L_2	15 mm

Setting angle κ	93 degrees
Shank $\varnothing D_s$	16 mm
Application type	right-hand
Boring depth up to	5xD
Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

Accessories

Clamping screw	269409
Clamping screw Type 6	269022 6