

**Garant**

**Blade carrier, concave for face grooving, left-hand, Ø range Groove D1 / D2:  
26/34mm**



## Order data

Order number	273825 26/34
GTIN	4045197577375
Item class	21W

## Description

**Version:**

Extremely rigid connection and precise clamping due to serrated contact face between the toolholder and clamp.

**Application:**

In conjunction with toolholders No. 273800 to 273811.

**Spare part:**

Clamp screw No. 279815 9.

**Attention:**

Without clamping screws (these are supplied with the toolholders).

**Note:**

$D_1$  = minimum Ø for the first groove /  $D_2$  = maximum Ø for the first cut.

Technology values should be reduced by 30 – 50% depending on the clamping situation and material.

Groove width w: 2 mm

maximum cutting depth  $t_{\max}$ : 13 mm

## Technical description

minimum 1st groove $\varnothing D_1$	26 mm
maximum 1st groove $\varnothing D_2$	34 mm
maximum cutting depth $t_{\max}$	13 mm
Application type	left-hand
Groove width w	2 mm
Type of product	Cartridges

---

## Accessories

Clamping screw	279910
Clamping screw Type 9	279815 9