

**Value pack 5 pcs. vanadium combination pliers, bright finish, with 2-component grips****Order data**

Order number	GG6010 160
GTIN	4069515045186
Item class	GGN

Description**Version:**

Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); suitable even for piano wire.

Jaws bright finished, handles with multi-component covering.

Standard:

DIN ISO 5746

Material:

Chrome vanadium steel, drop forged.

Supplied with:

5 pcs. combination pliers No.702995 size 160.

Technical description

Cutting capacity hard wire up to Ø	2 mm
overall length	160 mm
Cutting capacity piano wire up to Ø	1.5 mm
Standard	DIN ISO 5746
Jaw characteristics	inner face serrated

Data sheet

Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC), pliers body drop forged
Material	Chromium vanadium steel
Surface	bright finish
non-sparking	no
Type of product	Multi-function pliers
USP1	5 pcs. vanadium combination pliers, bright finished, with two-component grips

Suitable products

No Shop URL available for: GG6010 160