

Garant**Value pack 5 pcs. electronics side cutter clean cut, stronger jaws****Order data**

Order number	GG6014 135
GTIN	4069515045223
Item class	GGN

Description**Version:**

Professional diagonal side cutter with slightly shearing cut. Both cutter parts are very accurately put together using carefully machined holes and polished surfaces to ensure a precise cut. With opening spring and ergonomically designed handles for secure and comfortable use. **2-component grips** of dissipative material. **Suitable for ESD work.**

Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

Supplied with:

5 pcs. electronics side cutter No. 726702 size 135.

Technical description

Cutting capacity copper wire up to Ø	1.3 mm
Head width	13.5 mm
Cutter length	8 mm
overall length	135 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	Carbon steel (C70)

Data sheet

Surface	phosphated, non-reflecting
Product name attribute	KW
with return spring	yes
Type of product	Cutting pliers
USP1	5 pcs. electronics side cutter clean cut, stronger jaws

Suitable products

No Shop URL available for: GG6014 135