

Garant**Value pack 4 pcs. soft-faced hammer with nylon inserts****Order data**

Order number	GG6022 40
GTIN	4069515045285
Item class	GGN

Description**Version:**

Sturdy metal central piece with handle of hickory, with nylon handle protection sleeve and ring wedge. The nylon inserts are impact resistant and wear-resistant, and are attached to the central piece by a double action system.

Central piece of steel.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Supplied with:

4 pcs. soft-faced hammer incl. nylon inserts No. 754120 size 40.

Spare part:

Spare nylon insert available under No. 754180 and spare handle available under No. 751650.

Technical description

Handle length	320 mm
Head length with inserts	105 mm
Weight	0.578 kg
Hammer head Ø	40 mm
Type of product	Hammer

USP1

4 pcs. soft-faced hammer
with nylon inserts

Suitable products

No Shop URL available for: GG6022 40
