

**4 pcs. dead-blow hammer with steel tube handle, Hammer head Ø: 40mm****Order data**

| | |
|--------------|-----------|
| Order number | GG6023 40 |
| GTIN | |
| Item class | GGN |

Description**Version:**

Sturdy steel T-piece with exchangeable top quality wear-resistant nylon faces. **Dead-blow** effect achieved by steel ball filling in hammer head.

Steel tube handle with oil-resistant rubber grip.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Supplied with:

4 pcs. soft-faced hammer, dead-blow No. 754900 size 40.

Spare part:

For spare nylon face see No. 754910.

Technical description

| | |
|------------------------|------------|
| Hammer head Ø | 40 mm |
| Material of the handle | Steel tube |
| Weight | 0.805 kg |
| Material of body | Steel tube |
| Overall length | 300 mm |

Data sheet

| | |
|--------------------------|---|
| Material of insert | Nylon, white, hard |
| Series | SUPERCRAFT |
| Head length with inserts | 115 mm |
| Surface | Powder coated paint finish |
| dead-blow | yes |
| Type of product | Hammer |
| USP1 | 4 pcs. dead-blow hammer with steel tube handle |

Suitable products

No Shop URL available for: GG6023 40