

**Value pack 3 pcs. ideal snips with 2-component handles****Order data**

Order number	GG6026 260
GTIN	4069515045315
Item class	GGN

Description**Version:**

Drop-forged head, blades induction hardened. Adjustable pivot pins, double leverage with integrated return spring.

Ultra-fine serrated. Snip jaws made of **stainless steel** (HRC 58 – 60), handles of steel plate, nickel plated. 2-component handle with non-slip insert of soft material, easy on the hand.

Cutting capacity: Sheet metal up to 1.8 mm, stainless steel up to 1.2mm.

Application:

For continuous straight and shaped cutting.

Supplied with:

3 pcs. ideal snips, right-hand cutting No. 766042 size 260

Technical description

Length cutter	33 mm
overall length	260 mm
Application type	right-hand cutting
Type of product	Scissors
USP1	3 pcs. ideal snips with 2-component handles

Suitable products

No Shop URL available for: GG6026 260
