

**Value pack 3 pcs. corner pipe wrench with S-form jaws****Order data**

Order number	GG6030 1.1/2
GTIN	4069515045551
Item class	GGN

Description**Version:**

Swedish design, slim, specially formed jaws, self-tightening, offset 45°. Fully forged with captive adjustment nut.

HOLEX with **S-form jaws** for 3-point pipe support. (economy version).

Material:

Chrome vanadium steel; quenched and tempered, jaws induction hardened. Handles painted, jaws bright.

Supplied with:

3 pcs. corner pipe wrench, S-form jaws, No. 810600 size 1.1/2.

Technical description

Pipe Ø	1,1/2 in
Jaw capacity	63 mm
overall length	420 mm
Jaw angle	45 degrees
Manufacturing process	forged throughout
Hardened and tempered jaw	induction hardened
Material of pliers	Chromium vanadium steel
S-jaw	yes

Data sheet

Swedish profile	yes
Type of product	Pipe wrench and water pump pliers
USP1	3 pcs. corner pipe wrench with S-form jaws

Suitable products

No Shop URL available for: GG6030 1.1/2