

HOLEX®
TCMT 16T308 Set 10 pieces, Grade: HBX130

Order data

Order number	261030 HBX130
GTIN	4045197671288
Item class	22D

Description

TCMT 16T308 Set of 10 pieces HBX130 Grade: HBX130

Chip breaker: MM

Cutting depth a_p : 0.1 - 3.75 mm

Feed f : 0.06 - 0.3 mm/rev.

Cutting speed v_c main application: 60 - 200 m/min

Technical description

Chip breaker	MM
Main application	M
Cutting speed v_c main application	60 - 200 m/min
Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Cutting depth a_p	0.1 - 3.75 mm
Feed f	0.06 - 0.3 mm/rev.
Grade	HBX130

Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	TCMT 16T308
Number of changes/inserts	3
Type of product	Indexable insert for turning