

HOLEX®
Side lock arbor Form AD, SK 40 A = 100, Clamping range Ø D1: 20 mm

Order data

| | |
|--------------|---------------|
| Order number | 300260 20 |
| GTIN | 4045197143884 |
| Item class | 32A |

Description
Version:

With Balluffchip bore.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

External Ø D: 52 mm

Spare clamping screw 309900: 20

Technical description

| | |
|---------------------------------------|---------------------|
| Clamping Ø D ₁ | 20 mm |
| Spare clamping screw 309900 | 20 |
| External Ø D | 52 mm |
| Adapter | SK 40 A = 100 |
| Norm | DIN 6359 |
| Arbor standard | DIN 69871 |
| Arbor standard | ISO 7388-1 |
| Shape | AD |
| Balance quality G at rotational speed | G 6.3 at 15,000 rpm |
| Concentricity | ≤ 3 µm |

Machining strategy

HPC

Accessories

| | |
|---|-----------|
| Pull stud 90° sealed suitable for steep tapers 40 | 308795 40 |
|---|-----------|

| | |
|---|-----------|
| Special pull stud with no internal thread sealed suitable for steep tapers 40 | 308700 40 |
|---|-----------|

| | |
|---|-----------|
| Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40 | 308625 40 |
|---|-----------|

| | |
|---|-----------|
| Pull stud 45° sealed suitable for steep tapers 40 | 308760 40 |
|---|-----------|

| | |
|---|-----------|
| Special pull stud with no internal thread sealed suitable for steep tapers 40 | 308720 40 |
|---|-----------|

| | |
|---|-----------|
| Pull stud sealed, form B suitable for steep tapers 40 | 308650 40 |
|---|-----------|

| | |
|--|-----------|
| Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40 | 308615 40 |
|--|-----------|

| | |
|--|-----------|
| Pull stud Hurco 45° with fit sealed suitable for steep tapers 40 | 308802 40 |
|--|-----------|

| | |
|---|-----------|
| Pull stud 45° sealed suitable for steep tapers 40 | 308765 40 |
|---|-----------|

| | |
|--|------------|
| Pull stud Mazak sealed, form A suitable for steep tapers 40M | 308670 40M |
|--|------------|

| | |
|--|-----------|
| Pull stud Hurco 90° with fit sealed suitable for steep tapers 40 | 308806 40 |
|--|-----------|

| | |
|---|-----------|
| Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40 | 308630 40 |
|---|-----------|

| | |
|---|-----------|
| Special pull stud with internal thread suitable for steep tapers 40 | 308740 40 |
|---|-----------|

| | |
|--|-----------|
| Pull stud stud sealed, form A suitable for steep tapers 40 | 308610 40 |
|--|-----------|

| | |
|---|-----------|
| Pull stud 60° sealed suitable for steep tapers 40 | 308785 40 |
|---|-----------|

| | |
|---|-----------|
| Pull stud sealed suitable for steep tapers 40 | 308660 40 |
|---|-----------|

| | |
|---|-----------|
| Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK | 308810 40 |
|---|-----------|

| | |
|---|-----------|
| Pull stud Form A suitable for steep tapers 40 | 308600 40 |
|---|-----------|

| | |
|--|-----------|
| Pull stud sealed suitable for steep tapers 40 | 308635 40 |
| Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK | 308812 40 |
| Pull stud 90° sealed suitable for steep tapers 40 | 308790 40 |
| Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 40 SK | 308820 40 |
| Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40 | 308801 40 |
| Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40 | 308605 40 |
| Pull stud Form B suitable for steep tapers 40 | 308640 40 |
| Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 40 SK | 308830 40 |
| Pull stud sealed, form B suitable for steep tapers 40 | 308620 40 |