

Garant

45° turning/chamfering insert, internal, left-hand, L1 = 15 mm, Ø Dmin: 6,2 mm


Order data

Order number	270398 6,2
GTIN	4045197588784
Item class	211

Description

45° turning/chamfering insert, internal, left-hand 6,2 mm
 Shank Ø d: 6 mm
 Tip centre offset L₃: 2.95 mm
 maximum cutting depth t_{max}: 1.75 mm
 Radius R: 0.2 mm

Technical description

Shank Ø d	6 mm
maximum cutting depth t _{max}	1.75 mm
Tip centre offset L ₃	2.95 mm
Minimum Ø D _{min}	6.2 mm
Overhang L ₁	25 mm
Radius R	0.2 mm
Product name attribute	L ₁ = 15 mm