

HOLEX®
Side lock arbor Form AD, SK 40 A = 100, Clamping range \varnothing D1: 8 mm

Order data

Order number	300260 8
GTIN	4045197143822
Item class	32A

Description
Version:

With Balluffchip bore.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

External \varnothing D: 28 mm

Spare clamping screw 309900: 8

Technical description

Clamping \varnothing D ₁	8 mm
Spare clamping screw 309900	8
External \varnothing D	28 mm
Adapter	SK 40 A = 100
Norm	DIN 6359
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	$\leq 3 \mu\text{m}$

Machining strategy

HPC

Accessories

Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 40 SK

308820 40

Special pull stud with internal thread suitable for steep tapers 40

308740 40

Pull stud Hurco 45° with fit sealed suitable for steep tapers 40

308802 40

Pull stud sealed suitable for steep tapers 40

308660 40

Pull stud sealed, form B suitable for steep tapers 40

308620 40

Pull stud Form B suitable for steep tapers 40

308640 40

Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK

308812 40

Pull stud 45° sealed suitable for steep tapers 40

308760 40

Special pull stud with no internal thread sealed suitable for steep tapers 40

308700 40

Pull stud Form A suitable for steep tapers 40

308600 40

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40

308625 40

Pull stud sealed, form B suitable for steep tapers 40

308650 40

Special pull stud with no internal thread sealed suitable for steep tapers 40

308720 40

Pull stud Mazak sealed, form A suitable for steep tapers 40M

308670 40M

Pull stud 60° sealed suitable for steep tapers 40

308785 40

Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40

308615 40

Pull stud 90° sealed suitable for steep tapers 40

308790 40

Pull stud stud sealed, form A suitable for steep tapers 40

308610 40

308806 40

Pull stud Hurco 90° with fit sealed suitable for steep tapers 40

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40

308630 40

Pull stud 45° sealed suitable for steep tapers 40

308765 40

Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40

308605 40

Pull stud sealed suitable for steep tapers 40

308635 40

Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK

308810 40

Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 40 SK

308830 40

Pull stud 90° sealed suitable for steep tapers 40

308795 40

Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40

308801 40