

Garant
Boring insert, internal, left-hand, L1 = 30 mm, Ø Dmin / W: 5,2/1 mm

Order data

Order number	270386 5,2/1
GTIN	4045197467386
Item class	211

Description

Boring insert, internal, left-hand 5,2/1 mm Shank Ø d: 5 mm
 Tip centre offset L_3 : 2.45 mm
 maximum cutting depth t_{max} : 0.7 mm
 flat groove depth t: 0.3 mm

Technical description

Tip centre offset L_3	2.45 mm
flat groove depth t	0.3 mm
Minimum Ø D_{min}	5.2 mm
Shank Ø d	5 mm
maximum cutting depth t_{max}	0.7 mm
Overhang L_1	30 mm
Product name attribute	$L_1 = 30$ mm