

Garant
eco toolholder, left-hand, Shank width b: 25mm

Order data

Order number	273846 25
GTIN	4045197517487
Item class	21W

Description
Version:

GARANT eco-system toolholders with internal coolant supply to the cutting edge.

Suitable for:

Blade carriers No. 273880 and 273890.

Supplied with:

Including assembly screws.

Note:

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. **317900** – **319886** and GARANT eco cutter carriers No. **273880** – **273891**. Technology values should be reduced by 30% to 50% depending on the clamping situation and material.

Through-coolant: yes

Head length L_1 : 20.5 mm

Overall length L: 109 mm

Screw: 279815 9

Technical description

Shank width b	25 mm
Head length L_1	20.5 mm
Screw	279815 9
Overall length L	109 mm
Series	Eco

Application type	left-hand
Through-coolant	yes
Type of product	Clamping toolholder

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Clamping screw Type 9	279815 9
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Clamping screw	279910