

**LOCTITE.****Instant adhesive, 3 g, Manufacturer ID: 454**

## Order data

Order number	083351 454
GTIN	4058093008935
Item class	04L

## Description

**Version:**

Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity.

**Application:**

Universal instant adhesive **gel**. Suitable for **virtually all materials**. Non-drip, ideal for applications on vertical surfaces or overhead.

**Note:**

Not available in all countries. Express delivery not possible.

## Technical description

Touch dry after	5 - 10 s
Manufacturer's designation	LOCTITE 454
Tensile shear strength	20.9 N/mm <sup>2</sup>
Labelling of hazardous substances	GHS07: Exclamation mark
Dynamic viscosity	150 - 450 mPas

Storage temperature	2 °C
Operating temperature range	-40 - 120 °C
Shape	Gel
Working life after date of manufacture	24 mo
Chemical basis	Ethyl cyanoacrylate
Density	1.05 g/cm <sup>3</sup>
Characteristics	does not penetrate into workpiece surface
Characteristics	non-drip
Suitable for material	Leather
Suitable for material	Metal
Suitable for material	Paper
Suitable for material	wood
Suitable for material	cardboard
Suitable for material	Plastic
Suitable for material	porous materials
Colour	transparent
hazardous goods class	9
Capacity	3 ml
Maximum gap size	0.15 mm
Product name attribute	3 g
Type of product	Instant adhesive