

Garant
eco boring bar, right-hand, Ø DS: 32mm

Order data

Order number	273850 32
GTIN	4045197517500
Item class	21W

Description
Version:

GARANT eco-system toolholders with internal coolant supply to the cutting edge.

Suitable for:

Blade carrier No. 273886.

Supplied with:

Including assembly screws.

Note:

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. **317900** – **319886** and GARANT eco cutter carriers No. **273880** – **273891**. Technology values should be reduced by 30% to 50% depending on the clamping situation and material.

Through-coolant: yes

Shank Ø D_s: 32 mm

Centre offset L₃: 18.5 mm

Overall length L: 250 mm

Screw: 279815 9

Technical description

Screw	279815 9
Centre offset L ₃	18.5 mm
Overall length L	250 mm
Shank Ø D _s	32 mm
Series	Eco
Application type	right-hand

Through-coolant	yes
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Clamping screw	279910
Clamping screw Type 9	279815 9
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500