

Garant

eco blade carrier, convex for face grooving, left-hand, Ø range Groove D1 / D2: 53/76mm


Order data

Order number	273887 53/76
GTIN	4045197516572
Item class	21W

Description
Application:

In conjunction with GARANT eco-toolholder No. **273840 – 273851**.

Attention:

Without clamping screws (these are supplied with the toolholders).

Note:

D_1 = minimum Ø for the first first groove / D_2 = minimum Ø for the second groove.

Through-coolant: yes

Groove width w: 3 mm

maximum cutting depth t_{max} : 13 mm

Clamping screw: 279815 9

Technical description

maximum 1st groove Ø D_2	76 mm
minimum 1st groove Ø D_1	53 mm
maximum cutting depth t_{max}	13 mm
Series	Eco
Clamping screw	279815 9
Application type	left-hand
Through-coolant	yes

Groove width w	3 mm
Type of product	Cartridges

Accessories

Clamping screw Type 9	279815 9
Clamping screw	279910