

## Garant

### eco boring bar, left-hand, Ø DS: 32mm



#### Order data

Order number	273851 32
GTIN	4045197517524
Item class	21W

#### Description

##### Version:

GARANT eco-system toolholders with internal coolant supply to the cutting edge.

##### Suitable for:

Blade carrier No. 273887.

##### Supplied with:

Including assembly screws.

##### Note:

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. **317900** – **319886** and GARANT eco cutter carriers No. **273880** – **273891**. Technology values should be reduced by 30% to 50% depending on the clamping situation and material.

Through-coolant: yes

Shank Ø D<sub>s</sub>: 32 mm

Centre offset L<sub>3</sub>: 18.5 mm

Overall length L: 250 mm

Screw: 279815 9

#### Technical description

Screw	279815 9
Centre offset L <sub>3</sub>	18.5 mm
Overall length L	250 mm
Shank Ø D <sub>s</sub>	32 mm
Series	Eco
Application type	left-hand

Through-coolant	yes
Type of product	Boring bar

---

## Accessories

Clamping screw	279910
Clamping screw Type 9	279815 9
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20