

Garant
eco toolholder, right-hand, Shank width b: 20mm


Order data

Order number	273845 20
GTIN	4045197517432
Item class	21W

Description

Version:

GARANT eco-system toolholders with internal coolant supply to the cutting edge.

Suitable for:

Blade carriers No. 273881 and 273891.

Supplied with:

Including assembly screws.

Note:

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. **317900** – **319886** and GARANT eco cutter carriers No. **273880** – **273891**. Technology values should be reduced by 30% to 50% depending on the clamping situation and material.

Through-coolant: yes

Head length L_1 : 20.5 mm

Overall length L: 94 mm

Screw: 279815 9

Technical description

Shank width b	20 mm
Head length L_1	20.5 mm
Screw	279815 9
Overall length L	94 mm
Series	Eco

Application type	right-hand
Through-coolant	yes
Type of product	Clamping toolholder

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Clamping screw Type 9	279815 9
Clamping screw	279910