

HOLEX®
Side lock arbor Form AD, SK 40 A = 160, Clamping range \varnothing D1: 14 mm

Order data

Order number	300280 14
GTIN	4045197143938
Item class	32A

Description
Version:

With Balluffchip bore.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

External \varnothing D: 44 mm

Spare clamping screw 309900: 12

Technical description

Clamping \varnothing D ₁	14 mm
Spare clamping screw 309900	12
External \varnothing D	44 mm
Adapter	SK 40 A = 160
Norm	DIN 6359
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	$\leq 3 \mu\text{m}$

Machining strategy

HPC

Accessories

Pull stud 45° sealed suitable for steep tapers 40	308760 40
---	-----------

Pull stud Mazak sealed, form A suitable for steep tapers 40M	308670 40M
--	------------

Pull stud stud sealed, form A suitable for steep tapers 40	308610 40
--	-----------

Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
---	-----------

Pull stud Form A suitable for steep tapers 40	308600 40
---	-----------

Pull stud 90° sealed suitable for steep tapers 40	308795 40
---	-----------

Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308820 40
--	-----------

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
---	-----------

Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
--	-----------

Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
--	-----------

Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK	308812 40
---	-----------

Pull stud sealed suitable for steep tapers 40	308660 40
---	-----------

Pull stud 45° sealed suitable for steep tapers 40	308765 40
---	-----------

Pull stud 60° sealed suitable for steep tapers 40	308785 40
---	-----------

Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
--	-----------

Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308810 40
---	-----------

Special pull stud with no internal thread sealed suitable for steep tapers 40	308720 40
---	-----------

Pull stud Form B suitable for steep tapers 40	308640 40
---	-----------

	308740 40
--	-----------

Special pull stud with internal thread suitable for steep tapers 40

Pull stud Hurco 90° with fit sealed suitable for steep tapers 40

308806 40

Special pull stud with no internal thread sealed suitable for steep tapers 40

308700 40

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40

308630 40

Pull stud sealed suitable for steep tapers 40

308635 40

Pull stud 90° sealed suitable for steep tapers 40

308790 40

Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 40 SK

308830 40

Pull stud sealed, form B suitable for steep tapers 40

308650 40

Pull stud sealed, form B suitable for steep tapers 40

308620 40