

Garant

eco blade carrier, convex for face grooving, right-hand, Ø range Groove D1 / D2: 90/130mm


Order data

| | |
|--------------|---------------|
| Order number | 273886 90/130 |
| GTIN | 4045197516510 |
| Item class | 21W |

Description
Application:

In conjunction with GARANT eco-toolholder No. **273840 – 273851**.

Attention:

Without clamping screws (these are supplied with the toolholders).

Note:

D_1 = minimum Ø for the first first groove / D_2 = minimum Ø for the second groove.

Through-coolant: yes

Groove width w: 3 mm

maximum cutting depth t_{max} : 13 mm

Clamping screw: 279815 9

Technical description

| | |
|---------------------------------|------------|
| maximum cutting depth t_{max} | 13 mm |
| minimum 1st groove Ø D_1 | 90 mm |
| maximum 1st groove Ø D_2 | 130 mm |
| Series | Eco |
| Clamping screw | 279815 9 |
| Application type | right-hand |
| Through-coolant | yes |

| | |
|-----------------|------------|
| Groove width w | 3 mm |
| Type of product | Cartridges |

Accessories

| | |
|-----------------------|----------|
| Clamping screw | 279910 |
| Clamping screw Type 9 | 279815 9 |