

**Value pack digital caliper with large display and square depth gauge, measuring range 150 mm, 0.01 mm reading****Order data**

Order number	404103 3
GTIN	
Item class	43A

Description**Version:**

Easy-to-read, high-contrast LCD display with 11 mm high characters. Modern energy-efficient measuring system, operational life approx. 3 years. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Lapped slides, the measuring faces are precision lapped. With square depth gauge.

Supplied with:

Incl. 1 battery No. 081560 size CR2032. per caliper. 3 pcs. calipers No. 412717 size 150.

Technical description

Scale divisions	0.01 mm
Depth gauge available	yes
Power supply	Battery-powered
Calibration	A1
Standard	ISO 13385
Digit height LCD display	11 mm

Data sheet

Depth gauge	rectangular 3.7×1.3
Measured value saving	MAHR reference-lock system
Scale divisions	0.0005 in
Measurement deviation E MPE	± 0.03 mm
Measuring range	0 - 150 mm
Working time	approx. 3 years
Reversible reading	mm / inch
#Number of batteries contained	3
Jaw length	40 mm
#Article no of the battery / rechargeable battery fitted	081560 CR2032
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal caliper
USP1	Digital caliper with large display and square depth gauge, measurement range 150 mm, graduations 0.01 mm

Suitable products

No Shop URL available for: 404103 3