

● steinel

Gluematic 5000 hot glue gun, Manufacturer's product number: 332716



Order data

| | |
|--------------|---------------|
| Order number | 083385 332716 |
| GTIN | 4007841332716 |
| Item class | 07E |

Description

Version:

Gluematic 5000 hot glue guns for hobbies and manual crafts, cordless operation, very high feed rate of approx. 22 g/min, warming-up time only 3 – 5 min.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Supplied with:

Glue gun with interchangeable glue nozzles, charger, **without glue sticks.**

Technical description

| | |
|---|----------------|
| Manufacturer's designation | Gluematic 5000 |
| Nominal voltage | 220 - 240 V |
| Power supply | Mains-powered |
| Warm-up time | 3 - 5 min |
| Power consumption | 120 W |
| maximum \varnothing of the glue stick | 11 mm |

| | |
|---------------------------|--------------|
| maximum delivery quantity | 22 g/min |
| Temperature range | 210 - 220 °C |
| Type of product | Hot glue gun |

Accessories

| | |
|--|---------------|
| Glue stick set, 20 pieces Manufacturer's product number 044930 | 083388 044930 |
| Glue stick set, 20 pieces Manufacturer's product number 048419 | 083388 048419 |