

**Garant**

**eco blade carrier, convex for face grooving, right-hand, Ø range Groove D1 / D2: 110/170mm**


**Order data**

|              |                |
|--------------|----------------|
| Order number | 273886 110/170 |
| GTIN         | 4045197516527  |
| Item class   | 21W            |

**Description**
**Application:**

In conjunction with GARANT eco-toolholder No. **273840 – 273851**.

**Attention:**

Without clamping screws (these are supplied with the toolholders).

**Note:**

$D_1$  = minimum Ø for the first first groove /  $D_2$  = minimum Ø for the second groove.

Through-coolant: yes

Groove width w: 3 mm

maximum cutting depth  $t_{max}$ : 13 mm

Clamping screw: 279815 9

**Technical description**

|                                 |            |
|---------------------------------|------------|
| maximum 1st groove Ø $D_2$      | 170 mm     |
| minimum 1st groove Ø $D_1$      | 110 mm     |
| maximum cutting depth $t_{max}$ | 13 mm      |
| Series                          | Eco        |
| Clamping screw                  | 279815 9   |
| Application type                | right-hand |
| Through-coolant                 | yes        |

|                 |            |
|-----------------|------------|
| Groove width w  | 3 mm       |
| Type of product | Cartridges |

---

## Accessories

|                       |          |
|-----------------------|----------|
| Clamping screw Type 9 | 279815 9 |
| Clamping screw        | 279910   |