

Swivel work chair TEXON, Skintec, with castors, low, Seat colour: BLACK



Order data

Order number	965461 BLACK
GTIN	4099883003648
Item class	96J

Description

Version:

TEXON swivel work chair with interchangeable cushion system. The cushion elements are simply mounted and fixed with a click. Encapsulated mechanism thanks to Clean Cover; closed, smooth surfaces. Star base made of aluminium, black-grey. With ergonomic adjustment options: Seat height adjustment, Auto-Motion technology (backrest and seat move along with the body), Flex-Back (backrest can be locked in three different positions), anti-shock protection (backrest cannot shoot forwards unintentionally after the lock is released). Ergonomically shaped backrest. Seat with integrated pelvic support and rounded front edge of the seat.

Soft, load-responsive braked safety double castors for hard floors.

Seat and backrest made of Skintec, very soft to the touch, particularly easy to clean (resistant to disinfectants) and hard-wearing and durable.

Standard:

DIN 68877

Technical description

Colour of seat material	black
Standard	DIN 68877

Data sheet

Backrest height	625 mm
Version	with castors
Series	TEXON
Type of height adjustment	Height adjustment lever
Synchro mechanism	yes
Height adjustment version	Gas pressure spring
Material of base	Aluminium matt powder coated
Roller version	Safety double castors for hard floors
Base version	Roller set
Seat depth	455 mm
Safe working load	150 kg
Material of seat surface	Skintec
Weight	18 kg
Seat width	480 mm
Load capacity chair	150 kg
Height adjustment range	450 - 620 mm
Type of product	Swivel work chair