

**Garant**
**eco toolholder, left-hand, Shank width b: 20mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 273846 20     |
| GTIN         | 4045197517470 |
| Item class   | 21W           |

**Description**
**Version:**

GARANT eco-system toolholders with internal coolant supply to the cutting edge.

**Suitable for:**

Blade carriers No. 273880 and 273890.

**Supplied with:**

Including assembly screws.

**Note:**

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. **317900** – **319886** and GARANT eco cutter carriers No. **273880** – **273891**. Technology values should be reduced by 30% to 50% depending on the clamping situation and material.

Through-coolant: yes

Head length  $L_1$ : 20.5 mm

Overall length L: 94 mm

Screw: 279815 9

**Technical description**

|                   |          |
|-------------------|----------|
| Screw             | 279815 9 |
| Shank width b     | 20 mm    |
| Head length $L_1$ | 20.5 mm  |
| Overall length L  | 94 mm    |
| Series            | Eco      |

|                  |                     |
|------------------|---------------------|
| Application type | left-hand           |
| Through-coolant  | yes                 |
| Type of product  | Clamping toolholder |

---

## Accessories

|  |             |
|--|-------------|
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20                            | 674248 TX20 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659906 500  |
| Clamping screw   | 279910      |
| Clamping screw Type 9  | 279815 9    |