


VBMT 160408, Grade: CA510

Order data

Order number	261184 CA510
GTIN	4960664699872
Item class	25E

Description

VBMT 160408 CA510 Grade: CA510

Chip breaker: HQ

Cutting depth a_p : 0.5 - 2 mm

Feed f : 0.05 - 0.25 mm/rev.

Cutting speed v_c main application: 140 - 450 m/min

Technical description

Corner radius	0.8 mm
Cutting conditions	continuous
Chip breaker	HQ
Main application	P
Cutting speed v_c main application	140 - 450 m/min
Feed f	0.05 - 0.25 mm/rev.
Cutting depth a_p	0.5 - 2 mm

Grade	CA510
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	VBMT 160408
Number of changes/inserts	2
Type of product	Indexable insert for turning